

Order Date				Contact Name			
Acct #				Acct Name			
Phone #				Fax #			
Tray #				Patient Name			

			PRISM		PD		
	SPH	CYL	AXIS	IN/OUT	UP/DN	DIST	NEAR
R							
L							

		ADD	SEG HT	BASE CR	OC HT	CTR THK - only	EDGE THK + only
R							
L							

\* LENS INFO:  UNCUT  EDGED  FINISHED<sup>1</sup> (frame-to-come)

FRAME INFO:  Plastic  Metal  Groove  Drill/Notch<sup>2</sup>

A	B	ED	DBL	EYE SIZE	COLOR	BRAND & MODEL #

Panto Tilt <sup>3</sup>	Wrap Angle <sup>3</sup>	Back Vertex <sup>3</sup>	Refracted Back Vertex <sup>3</sup>	Reading Distance <sup>3</sup>	Frame Curve <sup>3</sup>

FINISHING
Polish
No Polish
Bevel/Groove Front
Bevel/Groove 1/3-2/3
Bevel/Groove 50/50

COLOR / TINT LEVEL				
Transmission:	80%	50%	30%	
Gray	1	2	3	
Brown	1	2	3	
Green	1	2	3	
Amber	1	2		
Rose	1	2		
Pink	1			
Blue	1			
Yellow	1			

TINTING <sup>4</sup>
Solid
Gradient 50/50
Gradient 1/3-2/3
Double Gradient
UV (CR39 only)

CHECK THE AVAILABILITY GUIDES & MARK YOUR LENS DESIGN & MATERIAL SELECTIONS FROM THE LIST BELOW.

LENS DESIGNS
KODAK Digital Single Vision
Single Vision <input type="checkbox"/> Aspheric
KODAK DSII™ 5,3
KODAK Unique™ HD 5,3
KODAK Unique <sup>5</sup>
KODAK Unique DS <sup>5</sup>
KODAK Precise® <input type="checkbox"/> PB <input type="checkbox"/> Digital
KODAK Precise Short <input type="checkbox"/> PB <input type="checkbox"/> Digital
KODAK Concise® <input type="checkbox"/> Digital
KODAK SoftWear®
DirectTek™ <input type="checkbox"/> DirectTek Short
Navigator® <input type="checkbox"/> Navigator Short®
Navigator FBS <input type="checkbox"/> Navigator Short FBS
FT 28
FT 35
7x28
8x35 (Only available in 1.50)
LENS TREATMENTS
KODAK Clean&Clear™ UV
KODAK Clean&Clear™
KODAK Clear+™
Crizal® Avance UV™
Crizal Alize UV™
Crizal Easy UV™
BluCrystal™ (not available on KODAK Unique Lenses)
NO AR

### Frame Shape Template #:

Required for all KODAK DSII, Unique/HD and Unique DS Lenses, polarized lenses, finished jobs, tinted uncuts & other lenses +2.50 and higher.

Or, hand trace right eye & indicate the Nasal (N).  
If no (N) indicated, we assume it's a right-eye trace.

### FOOTNOTES

<sup>1</sup> With frame, send a copy of this form and place an orange Signetek address label on your package.

<sup>2</sup> Must include a pattern with drill/notch finished jobs.

<sup>3</sup> For optimal customization, please provide point of wear measurements for a KODAK DSII Lens and KODAK Unique HD Lens.

<sup>4</sup> Tinting available on cast progressives and single vision lenses: 1.50, Poly, 1.60 and 1.67. Tinting available on KODAK DSII, Unique/HD/DS, Precise/Short PB, DirectTek/Short, Navigator/Short FBS: 1.50, Poly and 1.67.  
For tinted uncuts, a shape must be provided.

<sup>5</sup> To expedite your KODAK DSII, Unique, Unique HD or Unique DS Lens order, please indicate frame shape above (template number or hand trace of right eye).

<sup>6</sup> Graphite Green only available for KODAK Unique, Unique HD, Single Vision, KODAK Digital Single Vision and Precise/Short PB.

LENS MATERIALS	COLOR		
Standard Resin 1.50			
Trivex®			
Polycarbonate			
Clear 1.60			
Clear 1.67			
Clear 1.74 ***			
BluTech® Indoor 1.56			
BluTech Outdoor 1.56			
Transitions® Signature® 1.50	Gry	Bm	Gm
Transitions Signature Trivex	Gry	Bm	
Transitions Signature Poly	Gry	Bm	Gm
Transitions Signature 1.60 ***	Gry	Bm	
Transitions Signature 1.67	Gry	Bm	Gm
Transitions Signature 1.74 ***	Gry	Bm	
Transitions XTRActive® 1.50 **	Gry		
Transitions XTRActive Trivex **	Gry		
Transitions XTRActive Poly **	Gry		
Transitions XTRActive 1.67 **	Gry		
Transitions Vantage® 1.50	Gry		
Transitions Vantage Trivex	Gry		
Transitions Vantage Poly	Gry		
PhotoViews® 1.50	Gry	Bm	
PhotoViews Poly	Gry	Bm	
Drivewear® 1.50 **			
Polarized 1.50	Gry	Bm	
Polarized Poly	Gry	Bm	
Polarized 1.60 ***	Gry	Bm	
Polarized 1.67 ***	Gry	Bm	Gm <sup>6</sup>
Polarized 1.74 **	Gry	Bm	Gm <sup>6</sup>
Trivex Polarized **	Gry	Bm	
NXT Photochromic Polarized **	Gry	Bm	Amb
NXT Photochromic **	Gry	Bm	Gm
NXT Fixed Tint **	Gry	Bm	Gm
NXT Mirror **	Sliv	Gld	

\*\*\*THESE MATERIALS ARE ONLY AVAILABLE IN KODAK UNIQUE/HD AND SINGLE VISION.  
\*\*THESE MATERIALS ARE ONLY AVAILABLE IN KODAK DSII, UNIQUE/HD AND SINGLE VISION.

### SPECIAL INSTRUCTIONS: