

Order Date	Contact Name
Acct #	Acct Name
Phone #	Fax #
Tray #	Patient Name

	PRISM			PD			
	SPH	CYL	AXIS	IN/OUT	UP/DN	DIST	NEAR
R							
L							

	ADD	SEG HT	BASE CR	OC HT	CTR THK - only	EDGE THK + only
	R					
L						

* **LENS INFO:** UNCUT EDGED FINISHED¹ (frame-to-come)

FRAME INFO: Plastic Metal Groove Drill/Notch²

A	B	ED	DBL	EYE SIZE	COLOR	BRAND & MODEL #

Panto Tilt ³	Wrap Angle ³	Back Vertex ³	Refracted Back Vertex ³	Reading Distance ³	Frame Curve ³

FINISHING

Polish

No Polish

Bevel/Groove Front

Bevel/Groove 1/3-2/3

Bevel/Groove 50/50

COLOR / TINT LEVEL			
Transmission:	80%	50%	30%
Gray	1	2	3
Brown	1	2	3
Green	1	2	3
Amber	1	2	
Rose	1	2	
Pink	1		
Blue	1		
Yellow	1		

TINTING⁴

Solid

Gradient 50/50

Gradient 1/3-2/3

Double Gradient

UV (CR39 only)

CHECK THE AVAILABILITY GUIDES & MARK YOUR LENS DESIGN & MATERIAL SELECTIONS FROM THE LIST BELOW.

LENS DESIGNS
KODAK Digital Single Vision
Single Vision <input type="checkbox"/> Aspheric
KODAK DSII™ 5.3
KODAK Unique™ HD 5.3
KODAK Unique ⁵
KODAK Unique DS ⁵
KODAK Precise® <input type="checkbox"/> PB <input type="checkbox"/> Digital
KODAK Precise Short <input type="checkbox"/> PB <input type="checkbox"/> Digital
KODAK Concise® <input type="checkbox"/> Digital
KODAK SoftWear®
DirectTek™ <input type="checkbox"/> DirectTek Short
Navigator® <input type="checkbox"/> Navigator Short®
Navigator FBS <input type="checkbox"/> Navigator Short FBS
FT 28
FT 35
7x28
8x35 (Only available in 1.50)
LENS TREATMENTS (not to be combined with Total Blue Lens that already has AR included)
KODAK Clean&Clear™ UV
KODAK Clean&Clear™
KODAK ClearAR™
Crizal® Avance UV™
Crizal Alize UV™
Crizal Easy UV™
BluCrystal™ (not available on KODAK Unique Lenses)
NO AR

Frame Shape Template #:

Required for all KODAK DSII, Unique/HD and Unique DS Lenses, polarized lenses, finished jobs, tinted uncuts & other lenses +2.50 and higher.
Or, hand trace right eye & indicate the Nasal (N).
If no (N) indicated, we assume it's a right-eye trace.

FOOTNOTES

- With frame, send a copy of this form and place an orange Signetek address label on your package.
- Must include a pattern with drill/notch finished jobs.
- For optimal customization, please provide point of wear measurements for a KODAK DSII Lens and KODAK Unique HD Lens.
- Tinting available on cast progressives and single vision lenses: 1.50, Poly, 1.60 and 1.67. Tinting available on KODAK DSII, Unique/HD/DS, Precise/Short PB, DirectTek/Short, Navigator/Short FBS: 1.50, Poly and 1.67. Tinting not available on Total Blue Lenses. For tinted uncuts, a shape must be provided.
- To expedite your KODAK DSII, Unique, Unique HD or Unique DS Lens order, please indicate frame shape above (template number or hand trace of right eye).
- Graphite Green only available for KODAK Unique, Unique HD, Single Vision, KODAK Digital Single Vision and Precise/Short PB.

SPECIAL INSTRUCTIONS:

LENS MATERIALS	COLOR		
Standard Resin 1.50			
Trivex®			
EvoClear® II 1.56			
Polycarbonate			
Clear 1.60			
Clear 1.67			
Clear 1.74 ***			
BluTech® Indoor 1.56			
BluTech Outdoor 1.56 (polarized)			
Transitions® Signature® 1.50	Gry	Brn	Gm
Transitions Signature Trivex®	Gry	Brn	
Transitions Signature Poly	Gry	Brn	Gm
Transitions Signature 1.60 ***	Gry	Brn	
Transitions Signature 1.67	Gry	Brn	Gm
Transitions Signature 1.74 ***	Gry	Brn	
Transitions XTRActive® 1.50 **	Gry		
Transitions XTRActive Trivex **	Gry		
Transitions XTRActive Poly **	Gry		
Transitions XTRActive 1.67 **	Gry		
Transitions Vantage® 1.50	Gry		
Transitions Vantage Trivex	Gry		
Transitions Vantage Poly	Gry		
PhotoViews® 1.50	Gry	Brn	
PhotoViews Poly	Gry	Brn	
Drivewear® 1.50 **			
Polarized 1.50	Gry	Brn	
Polarized Trivex**	Gry	Brn	
Polarized Poly	Gry	Brn	
Polarized 1.60 ***	Gry	Brn	
Polarized 1.67 ***	Gry	Brn	Gm ⁵
Polarized 1.74 **	Gry	Brn	Gm ⁵

LENS MATERIAL WITH AR TREATMENT INCLUDED

Total Blue™ Lens 1.56			
Total Blue Lens 1.67			
Total Blue Lens 1.74			
Total Blue Lens Polarized 1.50	Gry		
Total Blue Lens Polarized Poly	Gry		
Total Blue Lens Polarized 1.67	Gry		
Total Blue Lens Polarized 1.74	Gry		

***THESE MATERIALS ARE ONLY AVAILABLE IN KODAK UNIQUE/HD AND SINGLE VISION.
***THESE MATERIALS ARE ONLY AVAILABLE IN KODAK DSII, UNIQUE/HD AND SINGLE VISION.