

Order Date			Contact Name				
Acct #			Acct Name				
Phone #			Fax #				
Tray #			Patient Name				

	PRISM			PD			
	SPH	CYL	AXIS	IN/OUT	UP/DN	DIST	NEAR
R							
L							

  

	ADD	SEG HT	BASE CR	OC HT	CTR THK - only	EDGE THK + only
	R					
L						

\* **LENS INFO:**  UN CUT  EDGED  FINISHED<sup>1</sup> (frame-to-come)

**FRAME INFO:**  Plastic  Metal  Groove  Drill/Notch<sup>2</sup>

A	B	ED	DBL	EYE SIZE	COLOR	BRAND & MODEL #

Panto Tilt <sup>3</sup>	Wrap Angle <sup>3</sup>	Back Vertex <sup>3</sup>	Refracted Back Vertex <sup>3</sup>	Reading Distance <sup>3</sup>	Frame Curve <sup>3</sup>

FINISHING
Polish
No Polish
Bevel/Groove Front
Bevel/Groove 1/3-2/3
Bevel/Groove 50/50

TINTING <sup>4</sup>
Solid
Gradient 50/50
Gradient 1/3-2/3
Double Gradient
UV (CR39 only)

COLOR / TINT LEVEL			
Transmission:	80%	50%	30%
Gray	1	2	3
Brown	1	2	3
Green	1	2	3
Amber	1	2	
Rose	1	2	
Pink	1		
Blue	1		
Yellow	1		

CHECK THE AVAILABILITY GUIDES & MARK YOUR LENS DESIGN & MATERIAL SELECTIONS FROM THE LIST BELOW.

LENS DESIGNS
KODAK Digital Single Vision
Single Vision <input type="checkbox"/> Aspheric
KODAK Unique DS™ <sup>5</sup>
KODAK Unique™ HD <sup>5,3</sup>
KODAK Unique™ <sup>5</sup>
KODAK Precise® <input type="checkbox"/> PB <input type="checkbox"/> Digital
KODAK Precise Short <input type="checkbox"/> PB <input type="checkbox"/> Digital
KODAK Concise® <input type="checkbox"/> Digital
KODAK MonitorView™
DirectTek™ <input type="checkbox"/> DirectTek Short
Navigator® <input type="checkbox"/> Navigator Short
FT 28
FT 35
7x28
8x35 (Only available in 1.50)
LENS TREATMENTS
KODAK Clean'N'Clear™
KODAK Clear™
Crizal® Avance UV™
Crizal Alize UV™
Crizal Easy UV™
BluCrystal™ (not available on KODAK Unique Lenses)
NO AR
LENS ADD-ONS
Anti-Fatigue Progressive Technology

LENS MATERIALS	COLOR		
Standard Resin 1.50			
Trivex®			
Polycarbonate			
Clear 1.60			
Clear 1.67			
Clear 1.74 **			
BluTech Indoor 1.56			
BluTech Outdoor 1.56			
Transitions® Signature 1.50	Gry	Bm	
Transitions Signature Trivex	Gry	Bm	
Transitions Signature Poly	Gry	Bm	
Transitions Signature 1.60 **	Gry	Bm	
Transitions Signature 1.67	Gry	Bm	
Transitions Signature 1.74 **	Gry	Bm	
Transitions XTRActive 1.50 **	Gry		
Transitions XTRActive Trivex **	Gry		
Transitions XTRActive Poly **	Gry		
Transitions XTRActive 1.67 **	Gry		
Transitions Vantage™ 1.50	Gry		
Transitions Vantage Trivex	Gry		
Transitions Vantage Poly	Gry		
PhotoViews 1.50	Gry	Bm	
PhotoViews Poly	Gry	Bm	
Life Rx™ Poly **	Gry	Bm	
Drivewear® 1.50 **			
Polarized 1.50	Gry	Bm	
Polarized Poly	Gry	Bm	
Polarized 1.60 **	Gry	Bm	
Polarized 1.67 **	Gry	Bm	
NXT Polarized **	Gry	Bm	
NXT Photochromic Polarized **	Gry	Bm	Amb
NXT Photochromic **	Gry	Bm	Amb
NXT Fixed Tint **	Gry	Bm	Gm
NXT Mirror **	Silv	Gld	

\*\*THESE MATERIALS ARE ONLY AVAILABLE IN KODAK UNIQUE AND SINGLE VISION.

### Frame Shape Template #:

Required for all KODAK Unique /HD and Unique DS Lenses, polarized lenses, finished jobs, tinted uncuts & other lenses +2.50 and higher.

Or, hand trace right eye & indicate the Nasal (N). If no (N) indicated, we assume it's a right-eye trace.

### FOOTNOTES

<sup>1</sup>With frame, send a copy of this form and place an orange Signetek address label on your package.

<sup>2</sup>Must include a pattern with drill/notch finished jobs.

<sup>3</sup>For optimal customization, please provide point of wear measurements for a Kodak Unique HD Lens.

<sup>4</sup>Tinting available on cast progressives and single vision lenses: 1.50, Poly, 1.60 and 1.67. Tinting available on KODAK Unique, Unique DS, Precise/Short PB, DirectTek/Short: 1.50 and 1.67. For tinted uncuts, a shape must be provided.

<sup>5</sup>To expedite your KODAK Unique, Unique HD or Unique DS Lens order, please indicate frame shape above (template number or hand trace of right eye).

### SPECIAL INSTRUCTIONS: