

1) CHECK AVAILABILITY GUIDES; 2) MARK YOUR LENS DESIGN & MATERIAL SELECTIONS BELOW.

| | | | |
|--------------|--|--------------|--|
| * Order Date | | Contact Name | |
| Acct # | | Acct Name | |
| Phone # | | Fax # | |
| Tray # | | Patient Name | |

| | | | PRISM | | PD | | |
|---|-----|-----|--------|---------|-------|----------------|-----------------|
| | SPH | CYL | AXIS | IN/OUT | UP/DN | DIST | NEAR |
| R | | | | | | | |
| L | | | | | | | |
| | | ADD | SEG HT | BASE CR | OC HT | CTR THK - only | EDGE THK + only |
| R | | | | | | | |
| L | | | | | | | |

| * LENS INFO: <input type="checkbox"/> UNCUT <input type="checkbox"/> EDGED <input type="checkbox"/> FINISHED ^{1,A} (frame-to-come) | | | | | | |
|---|---|----|-----|----------|-------|-----------------|
| FRAME INFO: <input type="checkbox"/> Plastic <input type="checkbox"/> Metal <input type="checkbox"/> Groove <input type="checkbox"/> Drill/Notch ² | | | | | | |
| A | B | ED | DBL | EYE SIZE | COLOR | BRAND & MODEL # |
| | | | | | | |

| Panto Tilt ³ | Wrap Angle ³ | Fit Back Vertex ³ | Refracted Back Vertex ³ | Reading Distance ³ | Frame Curve ³ |
|-------------------------|-------------------------|------------------------------|------------------------------------|-------------------------------|--------------------------|
| | | | | | |

| FINISHING | | | | |
|------------------------|--|--|--|--|
| Polish | | | | |
| No Polish | | | | |
| Bevel/Groove Front | | | | |
| Bevel/Groove 1/3-2/3 | | | | |
| Bevel/Groove 50/50 | | | | |
| TINTING ^{4,A} | | | | |
| Solid | | | | |
| Gradient 50/50 | | | | |
| Gradient 1/3-2/3 | | | | |
| Double Gradient | | | | |
| UV (CR39 only) | | | | |

| COLOR / TINT LEVEL (Clear CR-39 ³ & poly lenses only) | | | | |
|---|-----|-----|-----|--|
| Transmission: | 80% | 50% | 30% | |
| Gray | 1 | 2 | 3 | |
| Brown | 1 | 2 | 3 | |
| Green | 1 | 2 | 3 | |
| Amber | 1 | 2 | | |
| Rose | 1 | 2 | | |
| Pink | 1 | | | |
| Blue | 1 | | | |
| Yellow | 1 | | | |

| * LENS DESIGNS | |
|--|--|
| KODAK PowerUp® select one: <input type="checkbox"/> 0.40D <input type="checkbox"/> 0.66D | |
| KODAK Digital SV <input type="checkbox"/> Wrap ^A | |
| Single Vision <input type="checkbox"/> Aspheric | |
| KODAK DSII™ ^A | |
| KODAK Unique DRO® <input type="checkbox"/> Unique DRO HD ^A | |
| KODAK Unique™ <input type="checkbox"/> Unique HD ^A | |
| KODAK Precise® <input type="checkbox"/> PB <input type="checkbox"/> Digital | |
| KODAK Precise Short <input type="checkbox"/> PB <input type="checkbox"/> Digital | |
| KODAK Concise® <input type="checkbox"/> Digital | |
| KODAK SoftWear® | |
| Directek™ <input type="checkbox"/> Directek Short | |
| Navigator® FBS <input type="checkbox"/> Navigator Short FBS | |
| Navigator <input type="checkbox"/> Navigator Short® | |
| Crossbows™ Custom SV ^A <input type="checkbox"/> Junior | |
| Custom V ^A <input type="checkbox"/> Custom U | |
| Basic / 13mm <input type="checkbox"/> Basic / 17mm | |
| Flat-Top 28 <input type="checkbox"/> Flat-Top 35 | |
| 7x28 <input type="checkbox"/> 8x35 (Only available in 1.50) | |
| * LENS TREATMENTS | |
| KODAK Clean&CleAR™ UV <input type="checkbox"/> with Silk™ | |
| KODAK Clean&CleAR <input type="checkbox"/> with Silk | |
| KODAK CleAR+™ | |
| Crizal® Avance UV™ (N/A on 1.74, FT or Trifocal) | |
| Crizal Alize UV™ (N/A on 1.74, FT or Trifocal) | |
| Crizal Easy UV™ (N/A on 1.74, FT or Trifocal) | |
| BluCrystal™ (N/A on KODAK DSII/Unique/DRO/HD Lenses) | |
| NO AR | |

Frame Shape Template #: _____ *

^A Required for KODAK DSII, KODAK Unique/HD/DRO Lenses, Crossbows Custom V/Custom SV, polarized lenses, finished jobs, tinted uncuts & other lenses +2.50 and higher.
Or, hand trace right eye & indicate the Nasal (N).
If no (N) is indicated, we will assume it's a right-eye trace.

****MISSING INFORMATION WILL CAUSE DELAYS!**

FOOTNOTES

- ¹ With frame, send a copy of this form and place an orange Signetek address label on your package.
- ² Must include a pattern with drill/notch finished jobs.
- ³ For optimal customization, provide point-of-wear measurements for: KODAK DSII, Unique HD/ DRO HD Lenses; Crossbows V and SV designs.
- ⁴ Tinting available on clear CR-39 and poly lenses only. Tinting not available on photochromic, polarized, Total Blue Lens or KODAK KolorUp Sun Lens.
- ** Total Blue Lenses include a special AR coating that filters harmful high-energy visible (HEV) blue light. Ask for details.

| * LENS MATERIALS | | COLOR | | |
|--------------------------------------|------|-------|----------|--|
| Standard Resin 1.50 | | | | |
| Trivex® | | | | |
| EvoClear® II 1.56 | | | | |
| Polycarbonate | | | | |
| Clear 1.60 | | | | |
| Clear 1.67 | | | | |
| Clear 1.74 | | | | |
| Transitions® 1.50 | Gry | Brn | Grn | |
| Transitions Poly | Ambr | | Emerald | |
| Transitions 1.67 | Saph | | Amethyst | |
| Transitions Trivex | Gry | Brn | | |
| Transitions 1.60 | Gry | Brn | | |
| Transitions 1.74 | Gry | | | |
| Transitions XTRActive® 1.50 | Gry | | | |
| Transitions XTRActive Trivex | Gry | | | |
| Transitions XTRActive Poly | Gry | | | |
| Transitions XTRActive 1.67 | Gry | | | |
| Transitions Vantage® 1.50 | Gry | | | |
| Transitions Vantage Poly | Gry | | | |
| PhotoViews® 1.50 | Gry | Brn | | |
| PhotoViews Poly | Gry | Brn | | |
| Transitions Drivewear® 1.50 | | | | |
| KODAK KolorUp™ Sun Lens (Poly Tints) | Gry | Brn | Gy-Gn | |
| Polarized 1.50 | Gry | Brn | | |
| Polarized Trivex | Gry | Brn | | |
| Polarized Poly | Gry | Brn | | |
| Polarized 1.60 | Gry | Brn | | |
| Polarized 1.67 | Gry | Brn | Grn | |
| Polarized 1.74 | Gry | Brn | Grn | |

LENSES WITH COATING INCLUDED (DO NOT ADD AR)

| | | | | |
|---|------|--------|------|-------|
| Total Blue™ Lens** (clear) | Poly | 1.56 | 1.67 | 1.74 |
| Total Blue Polarized Lens** (gray base) | | | 1.50 | Poly |
| | | | 1.67 | 1.74 |
| Polar Poly Mirror (gray base) | Red | Silver | Blue | Green |

NOTE: CHECK AVAILABILITY GUIDES FOR DESIGN / LENS MATERIAL DETAILS.

SPECIAL INSTRUCTIONS: